


SE-1/SE-3

Single/Three-channel ECG



SE-1/SE-3

Single/Three-channel ECG

Technical Specifications

	SE-1 Single Channel ECG	SE-3 Three-Channel ECG
Input Circuit	Defibrillator protection built-in	
Lead	Standard 12 leads	
Acquisition Mode	Single lead	12 leads simultaneously
A/D Converter	12 bits	
Measurement Range	± 5mVpp	
Time Constant	> 3.2s	
Frequency Response	0.05Hz ~ 150Hz	
Calibration Voltage	1mV ± 3%	
Sensitivity	2.5, 5, 10, 20 (mm/mV)	
Input Impedance	> 10MΩ	> 50MΩ
Input Circuit Current	≤ 50nA	
Noise Level	<15 μVp-p	
Anti Baseline Drift	Auto	
Patient Leakage Current	< 10 μA (220V-240V)	
Patient Auxiliary Current	<0.1 μA (DC)	
Filter	EMG Filter 35Hz (-3dB) AC Filter 50 Hz/60Hz (-20dB)	EMG Filter 25Hz/35Hz/45Hz /OFF DFT Filter 0.05/0.15/0.25/0.5Hz Lowpass Filter 150Hz/100Hz/75Hz AC Filter 50 Hz/60Hz
CMRR	>90dB	>110dB
Recording Mode	Auto: 1CH, 1CH+1R Manual: 1CH	Auto: 3CH, 3/2 CH, 3CH+1R, 1CH, 1CH+1R Manual: 3CH, 3/2 CH, 1CH Rhythm: Single rhythm lead
Rhythm Lead	Any lead selectable	
Safety Standard	IEC I/CF	
Power Supply	AC: 100V-115V/220V-240V, 50/60Hz Built-in rechargeable Li-ion battery: voltage=14.4V More than 3 hrs continuous work under battery supply	
Recorder	Thermal printer	
Record Paper	50mm x 30m	80mmx20m
Paper Speed	25mm/s, 50mm/s (± 3%)	5mm/s, 6.25mm/s, 10mm/s, 12.5mm/s, 25mm/s 50mm/s (± 3%)
Dimension	288mm x 210mm x 70mm	
Weight	2.3kg (with battery)	2.5kg (with battery)
Display	192 x 64 pixels LCD	320 x 240 pixels LCD (Wide Screen) 192 x 64 pixels LCD (Narrow Screen)
External Input/Output	Input: > 100 kΩ ; Sensitivity 10mm/V ± 5% Output: < 100 Ω ; Sensitivity 1V/mV ± 5%	
Communication Interface	RS232	Ethernet, RS232

MARKETED IN INDIA BY :



MHS MEDICARE INDIA (P) LTD.

VENTILATOR
CPAP & BIPAP
PULSE OXIMETER
OXYGEN CONCENTRATOR
DEFIBRILLATOR WITH MONITOR * MULTIPARAMETER MONITOR

NEBULIZERS
CAPNOGRAPH
SLEEP LAB/SLEEP STUDY
PULSE OXIMETER & PROBES

Features and Specifications are subject to change without prior notice

, Inc.

Edan Instruments, Inc.
Edan Instruments, Inc. 1019# Shekou, Nanshan, Shenzhen, 518067 P.R. China
Tel: 86-755-2688 2223 Fax: 86-755-2688 2223 www.edan.com.cn Email: info@edan.com.cn

